



# Transformer



\*1M000000\*

Catalog Number

Type QL


**9T10A1006G61**

**150.0 KVA 60 HZ 3 PH 3.8 % IMP**

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

*Note: Design is based on 225.0KVA & 150C Rise 5.2% Imp.*

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 208 VOLTS (LINE-LINE)  
120 VOLTS (LINE-NEUTRAL)




JUMPER CONNECTION	
TAP	VOLTS
1-2	506
2-3	493
3-4	480
4-5	468
5-6	455
6-7	442
7-8	430

NET WGT  
1450 LB  
657.7 Kg

58576  
**DY77A**  
NOG  
010616

INSPECTION  
&  
FINAL TEST  
N602!

### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20) OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL Outline: 303B112GEDYP77A

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE

