



Transformer

by ABB




1M000000

Catalog Number 9T10A1122 **Type** QL


30.0 KVA 60 HZ 3 PH 5.3 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 480 VOLTS (LINE-LINE)
SECONDARY (H) 600 VOLTS (LINE-LINE)

JUMPER CONNECTION TAP	VOLTS
1	503
2	491
3	480
4	468
5	456
6	444
7	432



COIL TAP ARRANGEMENT



NET WGT
330 LB
149.7 Kg
88195
UX72A

INSPECTION & FINAL TEST
NOG
N139!
092021



H3 X3 H2 X2 H1 X1 - - - - -
H3 X3 H2 X2 H1 X1 - - - - -
H3 X3 H2 X2 H1 X1 - - - - -

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1 -
- - - - -
Note: standard

Outline: 303B111GEUXP72A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

