



# Transformer



\*1M000000\*

Catalog Number

Type QL


**9T10A1007G05**

**225.0 KVA 60 HZ 3 PH 5.2 % IMP**

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

*Note: Design is based on 225.0KVA & 150C Rise 5.2% Imp.*

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 208 VOLTS (LINE-LINE)  
120 VOLTS (LINE-NEUTRAL)



JUMPER CONNECTION	
TAP	VOLTS
1-2	506
2-3	493
3-4	480
4-5	468
5-6	455
6-7	442
7-8	430


NET WGT  
1450 LB  
657.7 Kg

58576  
DY77A

NOG  
121015

INSPECTION  
&  
FINAL TEST  
N550!

### COIL TAP ARRANGEMENT




ENCLOSURE TYPE 2 (IP20) OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001 Outline:  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL 303B112GEDYP77A

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE



\*2M000000\*



\*3M000000\*