



# Transformer

by ABB



\*1M0000000\*

**Catalog Number**

**9T10A1174G04**


**Type QL**

**75.0 KVA    60 HZ    3 PH    5.3 % IMP**  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C

**JUMPER  
CONNECTION  
TAP VOLTS**

- 1 503
- 2 492
- 3 480
- 4 467
- 5 456
- 6 445
- 7 430

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 480 VOLTS (LINE-LINE)  
277 VOLTS (LINE-NEUTRAL)



**NET WGT**  
561 LB  
254.5 Kg  
86144


UY74A  
NOG  
032621

INSPECTION  
&  
FINAL TEST  
N113!



LISTED 769G

### COIL TAP ARRANGEMENT



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE

ASSEMBLED IN MEXICO

**X3   H3   X2   H2   X1   H1**

Note: X0 at the bottom


Outline: 303B111GEUY74A

X3 H3 X2 H2 X1 H1



\*2M0000000\*

X3 H3 X2 H2 X1 H1



\*3M0000000\*

X0

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency