



Transformer

by ABB



1M000000

Catalog Number

9T10A1177G03



225.0 KVA 60 HZ 3 PH 4.8 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 480 VOLTS (LINE-LINE)
277 VOLTS (LINE-NEUTRAL)

Type QL

JUMPER CONNECTION

TAP	VOLTS
1-2	503
2-3	490
3-4	480
4-5	470
5-6	458
6-7	445
7-8	432



NET WGT	
1450 LB	INSPECTION & FINAL TEST
657.7 Kg	NOG
89198	N139!
DY77A	092021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

Note:

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

Outline: 303B112GEDYP77A



2M000000



3M000000