



Transformer

by ABB



1M000000



Catalog Number **Type QL**
9T10A1085G61

112.5 KVA **60 HZ** **3 PH** **2.8 % IMP**
40 C AMB. **80 C RISE** **220 C SYSTEM** **IS-19C**

Note: Design is based on 150.0KVA & 150C Rise 3.9% Imp.

PRIMARY (H) **480 VOLTS (LINE-LINE)**
SECONDARY (X) **400 VOLTS (LINE-LINE)**
 231 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1-2	502
2-3	491
3-4	480
4-5	468
5-6	456
6-7	445
7-8	433



NET WGT
1030 LB
467.2 Kg
89141
DY76A

INSPECTION & FINAL TEST
NOG
N137!
091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X3 - X2 - X1 - -
- H3 - H2 - H1

Note: X0 at the bottom

Outline: 303B111GEDYP76A

X0

- H1

- H2

- H3

- X1

- X2

- X3

2M000000

3M000000