



# Transformer

by ABB




\*1M000000\*

**Catalog Number**      **Type QL**  
**9T10A1104G03**


75.0 KVA    60 HZ    3 PH    6 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C

PRIMARY (H)    480 VOLTS (LINE-LINE)  
SECONDARY (X)    480 VOLTS (LINE-LINE)

JUMPER CONNECTION TAP	VOLTS
1	505
2	490
3	480
4	469
5	455
6	444
7	433



### COIL TAP ARRANGMENT



**NET WGT**  
561 LB  
254.5 Kg  
89153  
UY74A

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

**X3   H3   X2   H2   X1   H1**  
-   -   -   -   -   -  
Note: standard

Outline: 303B111GEUY74A

NEMA CLASS AA DRY TYPE TRANSFORMER


Meets DOE 2016 efficiency

X3 H3 X2 H2 X1 H1



\*2M000000\*

X3 H3 X2 H2 X1 H1



\*3M000000\*