



# Transformer

by ABB






\*1M000000\*

**Catalog Number**      **Type QL**  
**9T10A1115**


112.5 KVA    60 HZ    3 PH    5.2 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C

PRIMARY (X)    480 VOLTS (LINE-LINE)  
SECONDARY (H)    575 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	506
2-3	493
3-4	480
4-5	469
5-6	457
6-7	444
7-8	432



### COIL TAP ARRANGMENT



<b>NET WGT</b>	<b>INSPECTION &amp; FINAL TEST</b>
680 LB	
308.4 Kg	<b>NOG</b>
89159	<b>N137!</b>
DY75A	<b>091021</b>



LISTED 769G

H3 - H2 - H1 - X1

X3 - X2 - X1 - H1 - H2 - H1 - X3 - X2 - X1

H3 - H2 - H1 - X3 - X2 - X1

H3 - H2 - H1 - X3 - X2 - X1

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

H3 - H2 - H1 - -  
 - X3 - X2 - X1  
 Note: standard

Outline: 303B111GEDYP75A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*



\*3M000000\*