



Transformer

by ABB




1M000000

Catalog Number **Type QL**
9T10A1184G03


75.0 KVA 60 HZ 3 PH 6 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 240 VOLTS (LINE-LINE)
120 VOLTS (1 PH MIDTAP X1-X4)

JUMPER CONNECTION	TAP VOLTS
1	505
2	491
3	480
4	469
5	455
6	445
7	431



COIL TAP ARRANGEMENT



NET WGT
561 LB
254.5 Kg
89216
UY74A

INSPECTION & FINAL TEST
NOG
N137!
091021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06
REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X4 X3 H3 X2 H2 X1 H1

Note: MID-TAP

Outline: 303B111GEUY74A

H1	-	-	-	-	-	-	-
X1	-	-	-	-	-	-	-
H2	-	-	-	-	-	-	-
X2	-	-	-	-	-	-	-
H3	-	-	-	-	-	-	-
X3	-	-	-	-	-	-	-
H4	-	-	-	-	-	-	-
X4	-	-	-	-	-	-	-



2M000000



3M000000