



# Transformer

by ABB




\*1M000000\*

**Catalog Number**      **Type QL**  
**9T10A1332G31**


30.0 KVA    60 HZ    3 PH    5.8 % IMP  
40 C AMB.    115 C RISE    220 C SYSTEM    IS-19C

PRIMARY (X)    208 VOLTS (LINE-LINE)  
SECONDARY (H)    480 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1	218
2	212
3	208
4	202
5	198
6	192
7	186



### COIL TAP ARRANGMENT



<b>NET WGT</b>	<b>INSPECTION &amp; FINAL TEST</b>
444 LB	
201.4 Kg	<b>NOG</b>
88772	<b>N137!</b>
UX73A	<b>091021</b>



H3 X3 H2 X2 H1 X1 - - - - -  
H3 X3 H2 X2 H1 X1 - - - - -

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1 -

Note: standard

Outline: 303B111GEUXP73A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*



\*3M000000\*