



# Transformer

by ABB



\*1M000000\*


**Catalog Number** 9T10A1261 **Type** QL

15.0 KVA 60 HZ 3 PH 3.9 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


Note: Design is based on 15.00KVA & 115C Rise 3.7% Imp.

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 230 VOLTS (LINE-LINE)

JUMPER CONNECTION TAP	VOLTS
1	504
2	491
3	480
4	468
5	456
6	443
7	433



### COIL TAP ARRANGEMENT




NET WGT 231 LB  
104.8 Kg  
89235 UX71A  
INSPECTION & FINAL TEST  
NOG N139!  
092021



X3 H3 X2 H2 X1 H1



\*2M000000\*



\*3M000000\*

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 -

Note: standard

Outline: 303B111GEUXP71A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency