



Transformer



1M000000

Catalog Number


9T10A1345

Type QL

112.5 KVA 60 HZ 3 PH 2.9 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 112.5KVA & 115C Rise 2.9% Imp.



JUMPER CONNECTION	
TAP	VOLTS
1-2	219
2-3	214
3-4	208
4-5	202
5-6	196
6-7	191
7-8	185

NET WGT
1030 LB
467.2 Kg


53911
DY76A

NOG
020816

INSPECTION
&
FINAL TEST
N607!

PRIMARY (X) 208 VOLTS (LINE-LINE)
 SECONDARY (H) 480 VOLTS (LINE-LINE)
 277 VOLTS (LINE-NEUTRAL)

COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

Assembled in Mexico


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

Outline:
303B111GEDYP76A

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE

H3 - H2 - H1 - -
 - X3 - X2 - X1

Note: H0 at the bottom



2M000000



3M000000

H3 - H2 - H1 - -
 - X3 - X2 - X1
 H3 - H2 - H1 - -
 - X3 - X2 - X1

H0