



# Transformer

by ABB






\*1M000000\*

**Catalog Number** 9T10A1314 **Type** QL


75.0 KVA 60 HZ 3 PH 2.5 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 240 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	218
2-3	213
3-4	208
4-5	204
5-6	196
6-7	191
7-8	187



### COIL TAP ARRANGEMENT



**NET WGT**  
680 LB  
308.4 Kg  
89241  
DY75A

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



LISTED 769G

H3 - H2 - H1 -  
- X3 - X2 - X1 -  
H3 - H2 - H1 -  
- X3 - X2 - X1 -

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 - H2 - H1 - -  
- X3 - X2 - X1

Note: standard

Outline: 303B111GEDYP75A

