

# GE Transformer

—  
by ABB



\*1M000000\*


**Catalog Number**      **Type QL**  
**9T10A1347G31**

**225.0 KVA    60 HZ    3 PH    4.4 % IMP**  
**40 C AMB.    115 C RISE    220 C SYSTEM    IS-19C**


*Note: Design is based on 225.0KVA & 150C Rise 4.5% Imp.*

**PRIMARY (X)    208 VOLTS (LINE-LINE)**  
**SECONDARY (H)    480 VOLTS (LINE-LINE)**  
                                  **277 VOLTS (LINE-NEUTRAL)**

JUMPER CONNECTION	
TAP	VOLTS
1-2	220
2-3	214
3-4	208
4-5	202
5-6	195
6-7	189
7-8	183



### COIL TAP ARRANGEMENT



**NET WGT**      **INSPECTION & FINAL TEST**  
**1670 LB**      **757.5 Kg**  
**89282**      **NOG**  
**DY78A**      **N139!**  
                  **092021**



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

ASSEMBLED IN MEXICO


**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009**  
ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

Note:

Outline: 303B112GEDYP78A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*

\*3M000000\*