



# Transformer

by ABB



\*1M000000\*


**Catalog Number** 9T10A1323 **Type** QL

45.0 KVA 60 HZ 3 PH 3.8 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 240 VOLTS (LINE-LINE)  
120 VOLTS (1 PH MIDTAP H1-H4)

**JUMPER CONNECTION TAP VOLTS**

1	218
2	212
3	208
4	203
5	197
6	194
7	188



### COIL TAP ARRANGEMENT



**NET WGT**  
561 LB  
254.5 Kg  
89245  
UY74A

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



X1	-	-	-	-	-	-	-	-	-
H1	-	-	-	-	-	-	-	-	-
X2	-	-	-	-	-	-	-	-	-
H2	-	-	-	-	-	-	-	-	-
X3	-	-	-	-	-	-	-	-	-
H3	-	-	-	-	-	-	-	-	-
X4	-	-	-	-	-	-	-	-	-
H4	-	-	-	-	-	-	-	-	-



\*2M000000\*



\*3M000000\*

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H4 H3 X3 H2 X2 H1 X1

Note: MID-TAP

Outline: 303B111GEUY74A