



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10A1328 **Type** QL

300.0 KVA 60 HZ 3 PH 2.9 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

**JUMPER CONNECTION**  
**TAP VOLTS**  
1-2 220  
2-3 208  
3-4 200

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 240 VOLTS (LINE-LINE)  
120 VOLTS (1 PH MIDTAP H1-H4)



### COIL TAP ARRANGEMENT



**NET WGT** 2900 LB  
1315.4 Kg  
89248  
DX79A

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1079G06  
REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

ASSEMBLED IN MEXICO

Note:

Outline: 303B112GEDXP79A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*



\*3M000000\*