



Transformer

by ABB






1M000000

Catalog Number 9T10A1334 **Type** QL


75.0 KVA 60 HZ 3 PH 2.7 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)
SECONDARY (H) 480 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	218
2-3	213
3-4	208
4-5	204
5-6	196
6-7	191
7-8	187



COIL TAP ARRANGEMENT



NET WGT
680 LB
308.4 Kg
89252
DY75A

INSPECTION & FINAL TEST
NOG
N137!
091021



LISTED 769G

H3 - H2 - H1 -
- X3 - X2 - X1 -
H3 - H2 - H1 -
- X3 - X2 - X1 -

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 - H2 - H1 -
- X3 - X2 - X1
Note: standard

Outline: 303B111GEDYP75A

