



# Transformer

by ABB



\*1M000000\*


**Catalog Number** 9T10A1394 **Type** QL

75.0 KVA 60 HZ 3 PH 5.3 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

**JUMPER CONNECTION**

TAP	VOLTS
1	217
2	214
3	208
4	203
5	196

PRIMARY (X) 208 VOLTS (LINE-LINE)  
 SECONDARY (H) 400 VOLTS (LINE-LINE)  
 231 VOLTS (LINE-NEUTRAL)



### COIL TAP ARRANGEMENT



**NET WGT**  
 561 LB  
 254.5 Kg  
 89296  
 UY74A

**INSPECTION & FINAL TEST**  
 NOG  
 N137!  
 091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

H3	X3	H2	X2	H1	X1
-	-	-	-	-	-

Note: H0 at the bottom

Outline: 303B111GEUY74A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

H3 X3 H2 X2 H1 X1  
 H3 X3 H2 X2 H1 X1  
 H3 X3 H2 X2 H1 X1



\*2M000000\*



\*3M000000\*

H0