



# Transformer

—  
by ABB




\*1M000000\*

**Catalog Number** 9T10A1345G31  
**Type QL**


112.5 KVA 60 HZ 3 PH 2.8 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 480 VOLTS (LINE-LINE)  
277 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	
TAP VOLTS	
1-2	219
2-3	214
3-4	208
4-5	202
5-6	196



### COIL TAP ARRANGEMENT



NET WGT	INSPECTION & FINAL TEST
1030 LB	
467.2 Kg	NOG
89277	N137!
DY76A	091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 - H2 - H1 - -  
- X3 - X2 - X1

Note: H0 at the bottom

Outline: 303B111GEDYP76A

H3 - H2 - H1 - -

- X3 - X2 - X1

H3 - H2 - H1 -

- X3 - X2 - X1

H0

\*2M000000\*

\*3M000000\*