



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10A1392 **Type** QL


30.0 KVA 60 HZ 3 PH 4.9 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 400 VOLTS (LINE-LINE)  
231 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1	218
2	214
3	208
4	204
5	197
6	193
7	187



### COIL TAP ARRANGEMENT



**NET WGT**  
330 LB  
149.7 Kg  
89295  
UX72A

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1 H0

Note: standard

Outline: 303B111GEUXP72A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

H3	X3	H2	X2	H1	X1	H0
-	-	-	-	-	-	-
H3	X3	H2	X2	H1	X1	H0
-	-	-	-	-	-	-

\*2M000000\*

\*3M000000\*