



Transformer



1M000000

Catalog Number
9T10A1454G03

Type **QL**

75.0 KVA 60 HZ 3 PH 3.1 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 208 VOLTS (LINE-LINE)
SECONDARY (X) 208 VOLTS (LINE-LINE)
120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL


Outline:
303B111GEDYP75A

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE**

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



| JUMPER CONNECTION | |
|-------------------|-------|
| TAP | VOLTS |
| 1-2 | 218 |
| 2-3 | 213 |
| 3-4 | 208 |
| 4-5 | 205 |
| 5-6 | 196 |
| 6-7 | 191 |
| 7-8 | 187 |


NET WGT
680 LB
308.4 Kg

60320
DY75A

NOG
021216

INSPECTION
&
FINAL TEST
N607!

COIL TAP ARRANGEMENT



Assembled in Mexico

X3 - X2 - X1 - -
- H3 - H2 - H1

Note: X0 at the bottom

X1 - -
X2 - H1
H3 - H2 - H1
X3 - X1 - X0
X2 - X1 - H1
H3 - H2 - H1
X3 - X2 - H2
X3 - X2 - H2
H3 - H3 - H1
X3 - X2 - H2
X3 - X2 - H2
H3 - H3 - H1
X0



2M000000



3M000000