



Transformer

by ABB



1M000000

Catalog Number **Type QL**
9T10A1531G31


15.0 KVA **60 HZ** **3 PH** **3.6 % IMP**
40 C AMB. **115 C RISE** **220 C SYSTEM** **IS-19C**

Note: Design is based on 15.00KVA & 150C Rise 3.8% Imp.

PRIMARY (X) **240 VOLTS (LINE-LINE)**
SECONDARY (H) **480 VOLTS (LINE-LINE)**
 277 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION

TAP	VOLTS
1	252
2	245
3	240
4	234
5	228
6	222
7	215




NET WGT
231 LB
104.8 Kg
89328
UX71A

INSPECTION & FINAL TEST
NOG
N139!
092021



COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1 H0

Note: standard

Outline: 303B111GEUXP71A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

H3	X3	H2	X2	H1	X1	H0
-	-	-	-	-	-	-
H3	X3	H2	X2	H1	X1	H0
-	-	-	-	-	-	-

2M000000

3M000000