



# Transformer

by ABB



\*1M000000\*


**Catalog Number** 9T10A1551 **Type** QL

15.0 KVA 60 HZ 3 PH 4 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 15.00KVA & 115C Rise 4.2% Imp.

PRIMARY (X) 240 VOLTS (LINE-LINE)  
SECONDARY (H) 400 VOLTS (LINE-LINE)  
231 VOLTS (LINE-NEUTRAL)


JUMPER CONNECTION	TAP VOLTS
1	252
2	246
3	240
4	233
5	229
6	223
7	216



NET WGT 231 LB  
104.8 Kg  
89344 UX71A  
INSPECTION & FINAL TEST  
NOG N139!  
092021



### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1 H0

Note: standard

Outline: 303B111GEUXP71A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

H3	X3	H2	X2	H1	X1	H0
-	-	-	-	-	-	-
H3	X3	H2	X2	H1	X1	H0
-	-	-	-	-	-	-

\*2M000000\*

\*3M000000\*