



Core & Coil Transformer

by ABB



1M000000


Catalog Number **Type** QL-C
9T10B2407

225.0 KVA 60 HZ 3 PH 5.4 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


Note: Design is based on 225.0KVA & 150C Rise 5.4% Imp.

PRIMARY (H) 600 VOLTS (LINE-LINE)
SECONDARY (X) 208 VOLTS (LINE-LINE)
 120 VOLTS (LINE-NEUTRAL)

| JUMPER CONNECTION | |
|-------------------|-------|
| TAP | VOLTS |
| 1-2 | 632 |
| 2-3 | 613 |
| 3-4 | 600 |
| 4-5 | 588 |
| 5-6 | 569 |
| 6-7 | 556 |
| 7-8 | 537 |



COIL TAP ARRANGEMENT



| | |
|---|--|
| NET WGT 1290 LB 585.1 Kg 89443 DY77A | INSPECTION & FINAL TEST NOG N139! 092021 |
|---|--|



ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

Note:

Outline: 303B112GEDYP77A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



2M000000



3M000000