



# Transformer

—  
by ABB



\*1M000000\*

**Catalog Number**      **Type QL**  
**9T10C1001G31**


**15.0 KVA    60 HZ    3 PH    3.8 % IMP**  
**40 C AMB.    115 C RISE    220 C SYSTEM    IS-19C**

**PRIMARY (H)    480 VOLTS (LINE-LINE)**  
**SECONDARY (X)    208 VOLTS (LINE-LINE)**  
**120 VOLTS (LINE-NEUTRAL)**

JUMPER CONNECTION	
TAP	VOLTS
1	504
2	492
3	480
4	468
5	456
6	444
7	432



**COIL TAP ARRANGMENT**



**NET WGT**  
230 LB  
104.3 Kg  
89465  
UX71C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**

COPPER CONDUCTOR      PRIMARY: 10 KV BIL      SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

**X3    H3    X2    H2    X1    H1    X0**

Note: standard

Outline: 303B111GEUXP71C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X0  
X1  
H1  
-  
-  
-  
X2  
H2  
X2  
H2  
X2  
H2  
X3  
H3  
X3  
H3  
X3  
H3  
X3  
H3  
X0

