



Transformer

— by ABB



1M000000

Catalog Number **Type QL**


9T10C1002G32

30.0 KVA 60 HZ 3 PH 3.7 % IMP
40 C AMB. 115 C RISE 220 C SYSTEM IS-19C


Note: Design is based on 30.00KVA & 115C Rise 3.7% Imp.

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 208 VOLTS (LINE-LINE)
 120 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP	VOLTS
1	503	
2	493	
3	480	
4	468	
5	455	
6	445	
7	432	



COIL TAP ARRANGEMENT



NET WGT
353 LB
160.1 Kg
89478
UX72C

INSPECTION & FINAL TEST
NOG
N139!
092021



LISTED 769G

X0						
H1						
X1						
H2						
X2						
H3						
X3						

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 X0

Note: **standard**


NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

Outline: 303B111GEUXP72C



2M000000



3M000000