



# Transformer

—  
by ABB




\*1M000000\*

**Catalog Number**      **Type QL**  
**9T10C1005G33**


**112.5 KVA    60 HZ    3 PH    3.4 % IMP**  
**40 C AMB.    115 C RISE    220 C SYSTEM    IS-19C**

**PRIMARY (H)    480 VOLTS (LINE-LINE)**  
**SECONDARY (X)    208 VOLTS (LINE-LINE)**  
**120 VOLTS (LINE-NEUTRAL)**

JUMPER CONNECTION	TAP VOLTS
1-2	504
2-3	492
3-4	480
4-5	468
5-6	456
6-7	444
7-8	432



**COIL TAP ARRANGEMENT**



<b>NET WGT</b> 900 LB 408.2 Kg	<b>INSPECTION &amp; FINAL TEST</b> NOG N137! 091021
89505 DX75C	



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**

COPPER CONDUCTOR      PRIMARY: 10 KV BIL      SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.**

**CHECK ADDITIONAL NEC AND LOCAL CODE**

**ASSEMBLED IN MEXICO**

**X3 - X2 - X1 - -**  
**- H3 - H2 - H1**

Note: X0 at the bottom

Outline: 303B111GEDXP75C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

\*2M000000\*  
**X3 - X2 - X1 - -**  
**- H3 - H2 - H1**  
 \*3M000000\*  
**X3 - X2 - X1 - -**  
**- H3 - H2 - H1**  
 \*X0