



Transformer

by ABB



1M000000



Catalog Number **Type QL**
9T10C1005G63

112.5 KVA **60 HZ** **3 PH** **3.3 % IMP**
40 C AMB. **80 C RISE** **220 C SYSTEM** **IS-19C**

Note: Design is based on 150.0KVA & 150C Rise 4.4% Imp.

PRIMARY (H) **480 VOLTS (LINE-LINE)**
SECONDARY (X) **208 VOLTS (LINE-LINE)**
 120 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	
TAP	VOLTS
1-2	506
2-3	493
3-4	480
4-5	468
5-6	455
6-7	442
7-8	430



NET WGT	INSPECTION & FINAL TEST
1085 LB	
492.2 Kg	NOG
89512	N137!
DY76C	091021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR **PRIMARY: 10 KV BIL** **SECONDARY: 10 KV BIL**
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

X3 - X2 - X1 - -
- H3 - H2 - H1
Note: X0 at the bottom

Outline: 303B111GEDYP76C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X0

- H1

- H2

- H3

- X1

- X2

- X3

2M000000

3M000000