



# Transformer



\*1M000000\*

**Catalog Number**  
**9T10C1084G03**

**Type QL**

**75.0 KVA    60 HZ    3 PH 4.2 % IMP**

40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C


PRIMARY (H)    480 VOLTS (LINE-LINE)  
SECONDARY (X)    400 VOLTS (LINE-LINE)  
                          231 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE


ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001    Outline:  
COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL    303B111GEUY74C

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE**



### COIL TAP ARRANGEMENT



JUMPER CONNECTION	
TAP	VOLTS
1	502
2	493
3	480
4	466
5	457
6	444
7	431

NET WGT  
661 LB  
299.8 Kg  
  
60453  
UY74C  
NOG  
022516

INSPECTION  
&  
FINAL TEST  
N609!



Assembled in Mexico


**X3   H3   X2   H2   X1   H1   -**

Note: X0 at bottom


X3 H3 X2 H2 X1 H1

X3 H3 X2 H2 X1 H1

X0



\*2M000000\*



\*3M000000\*