

TYPICAL TEST DATA

LV Dry Type Transformer



MODEL #: **9T10C1008**

Underwriters' Laboratories Inc. Listed

RATINGS

KVA	300	Conductor	CU
Frequency (Hz)	60	Phase	3
Primary Voltage	480D +2, -4 (2.5% taps)	Secondary Voltage	208Y/120
Current Line Primary (A)	360.84	Current Line Secondary (A)	832.72
Frame	DY78C	Insulation System (°C)	220C
K Factor	1	Efficiency level	DoE 2016 (10CFR 431)
Temp. Rise (°C)	150	Average Sound Level (dB)	55

LOSS DATA @ 100% LOAD

Core Loss or No Load Loss @ 100% voltage (Watts)	478.2
Impedance Loss or Coil Loss @ Rise + 20 °C reference (Watts)	<u>5,844.3</u>
Total Loss @ Rise + 20 °C reference (Watts)	6,322.5

DIELECTRIC AND PRODUCTION TESTING

Induce Test @ Twice rated voltage 400 Hz per UL1561 and NEMA ST-20
 Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz, 60 Sec
 Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz, 60 Sec
 Polarity additive in accordance with UL1561 and NEMA ST-20

EFFICIENCY:

DoE 2016 (10CFR 431) Efficiency Level

<u>Load (%)</u>	<u>Efficiency (%)</u>
16	98.79
25	99.01
35	99.02
50	98.97
75	98.72
100	98.42

IMPEDANCE:

Impedance at reference temperature of Rise + 20 °C (Calculated)

%R	1.9
%X	4.5
%Z	4.9
X/R Ratio	2.4

REGULATION:

Regulation at reference temperature of Rise + 20 °C (Calculated)

<u>Power Factor</u>	<u>Regulation (%)</u>
1	2.1
0.9	4.0
0.8	4.6

REFERENCE VALUES:

Inrush Current (Calculated)	t= 8.33ms
I _{max} (RMS)	≈1804.22A