



# Transformer

by ABB





\*1M000000\*

**Catalog Number** 9T10C1146G31  
**Type** QL

150.0 KVA 60 HZ 3 PH 3.8 % IMP  
40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 480 VOLTS (LINE-LINE)  
SECONDARY (H) 600 VOLTS (LINE-LINE)  
346 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1-2	504
2-3	491
3-4	480
4-5	466
5-6	453
6-7	441
7-8	434



**NET WGT** 1240 LB  
**INSPECTION & FINAL TEST**  
 562.5 Kg  
**NOG**  
 89613  
**N137!**  
 DX76C  
 091021



H3 - H2 - H1 - -  
 - X3 - X2 - X1  
 H3 - H2 - H1 -  
 - X3 - X2 - X1  
 H0

\*2M000000\*

\*3M000000\*

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

H3 - H2 - H1 - -  
 - X3 - X2 - X1  
 Note: H0 at the bottom

Outline: 303B111GEDXP76C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency