



Transformer

—
by ABB





1M000000

Catalog Number **Type QL**
9T10C1016

150.0 KVA 60 HZ 3 PH 4.6 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 220 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	505
2-3	494
3-4	480
4-5	470
5-6	458
6-7	446
7-8	434



NET WGT	INSPECTION & FINAL TEST
1085 LB	
492.2 Kg	NOG
89546	N139!
DY76C	092021



X3 - X2 - X1 - - H3 - H2 - H1
X3 - X2 - X1 - - H3 - H2 - H1

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3 - X2 - X1 - -
- H3 - H2 - H1
Note: standard

Outline: 303B111GEDYP76C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



2M000000



3M000000