



Transformer

by ABB




1M000000

Catalog Number **Type QL**
9T10C1175G31


112.5 KVA 60 HZ 3 PH 2.8 % IMP
 40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
 SECONDARY (X) 480 VOLTS (LINE-LINE)
 277 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1-2	506
2-3	494
3-4	480
4-5	470
5-6	458
6-7	446
7-8	434



COIL TAP ARRANGEMENT



NET WGT 900 LB
 408.2 Kg
 89634
 DX75C
 INSPECTION & FINAL TEST
 NOG
 N137!
 091021



LISTED 769G

X3 - X2 - X1 - H3 - H2 - H1
 X3 - X2 - X1 - H3 - H2 - H1
 X3 - X2 - X1 - H3 - H2 - H1
 X0

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

ASSEMBLED IN MEXICO

X3 - X2 - X1 - -
 - H3 - H2 - H1
 Note: X0 at the bottom

Outline: 303B111GEDXP75C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency