



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10C1176 **Type** QL


150.0 KVA 60 HZ 3 PH 4.1 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 480 VOLTS (LINE-LINE)  
277 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1-2	504
2-3	491
3-4	480
4-5	466
5-6	453
6-7	441
7-8	435



### COIL TAP ARRANGEMENT



<b>NET WGT</b>	INSPECTION & FINAL TEST
1085 LB	TEST
492.2 Kg	NOG
89638	N139!
DY76C	092021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X3 - X2 - X1 - -  
 - H3 - H2 - H1

Note: X0 at the bottom

Outline: 303B111GEDYP76C

X3 - X2 - X1 - - H1  
 - H3 - H2 - H1  
 X3 - X2 - X1 - - X0  
 - H3 - H2 - H1

\*2M000000\*

\*3M000000\*