



# Transformer

by ABB



\*1M000000\*

**Catalog Number** 9T10C1073 **Type** QL


45.0 KVA 60 HZ 3 PH 3.1 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 380 VOLTS (LINE-LINE)  
219 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1	504
2	493
3	480
4	468
5	457
6	442
7	432



### COIL TAP ARRANGMENT



**NET WGT**  
480 LB  
217.7 Kg  
89571  
UX73C

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 -

Note: X0 at the top

Outline: 303B111GEUXP73C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X3 H3 X2 H2 X1 H1 -  
 X3 H3 X2 H2 X1 H1 -  
 X3 H3 X2 H2 X1 H1 -



X0