



Transformer

by ABB



1M000000


Catalog Number **Type** QL
9T10C1075G61

112.5 KVA 60 HZ 3 PH 3 % IMP
40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 150.0KVA & 150C Rise 4.2% Imp.

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 380 VOLTS (LINE-LINE)
 219 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	
TAP	VOLTS
1-2	501
2-3	489
3-4	480
4-5	470
5-6	458
6-7	445
7-8	433



NET WGT	INSPECTION & FINAL TEST
1085 LB	NOG
492.2 Kg	N139!
89577	092021
DY76C	



X3 - X2 - X1 - - H3 - H2 - H1
X3 - X2 - X1 - - H3 - H2 - H1
X0

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

ASSEMBLED IN MEXICO

X3 - X2 - X1 - -
- H3 - H2 - H1
Note: X0 at the bottom

Outline: 303B111GEDYP76C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

