



# Transformer



\*1M0000000\*

Catalog Number  
**9T10C1087G33**

Type **QL**

**225.0 KVA 60 HZ 3 PH 3.8 % IMP**

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C


PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 400 VOLTS (LINE-LINE)  
231 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE


ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001 Outline:  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL 303B112GEDXP77C

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE**



### COIL TAP ARRANGEMENT



JUMPER CONNECTION	
TAP	VOLTS
1-2	508
2-3	490
3-4	480
4-5	471
5-6	453
6-7	443
7-8	434

NET WGT  
1847 LB  
837.8 Kg

60531  
DK77C  
NOG  
030716

INSPECTION  
&  
FINAL TEST  
N611!



LISTED 769G

Assembled in Mexico



\*2M0000000\*



\*3M0000000\*