



Transformer

by ABB




1M000000

Catalog Number 9T10C1116 **Type** QL


150.0 KVA 60 HZ 3 PH 4.4 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 480 VOLTS (LINE-LINE)
SECONDARY (H) 575 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	503
2-3	491
3-4	480
4-5	467
5-6	455
6-7	443
7-8	431



COIL TAP ARRANGEMENT



NET WGT 1085 LB 492.2 Kg	INSPECTION & FINAL TEST NOG N139! 092021
89610 DY76C	



H3 - H2 - H1 -
- X3 - X2 - X1 -
H3 - H2 - H1 -
- X3 - X2 - X1 -

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 - H2 - H1 - -
- X3 - X2 - X1

Note: standard

Outline: 303B111GEDYP76C

