



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10C1131 **Type** QL


15.0 KVA 60 HZ 3 PH 4.1 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 440 VOLTS (LINE-LINE)  
254 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION TAP	VOLTS
1	504
2	492
3	480
4	469
5	457
6	443
7	431



### COIL TAP ARRANGEMENT



**NET WGT**  
230 LB  
104.3 Kg  
89611  
UX71C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 X0

Note: standard

Outline: 303B111GEUXP71C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X0  
X1  
H1  
X2  
H2  
X3  
H3



\*2M000000\*



\*3M000000\*