



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10C1334 **Type** QL


75.0 KVA 60 HZ 3 PH 5.6 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 480 VOLTS (LINE-LINE)

JUMPER CONNECTION TAP	VOLTS
1	218
2	213
3	208
4	204
5	196
6	191
7	187



### COIL TAP ARRANGEMENT



**NET WGT**  
748 LB  
339.3 Kg  
89699  
UX74C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



H3 X3 H2 X2 H1 X1  
- - - - -  
H3 X3 H2 X2 H1 X1  
- - - - -

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1

Note: standard

Outline: 303B111GEUXP74C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

