



**Catalog Number**      **Type QL**


**9T10C1174**

75.0 KVA    60 HZ    3 PH    4.9 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C


PRIMARY (H)    480 VOLTS (LINE-LINE)  
SECONDARY (X)    480 VOLTS (LINE-LINE)  
  277 VOLTS (LINE-NEUTRAL)

**JUMPER CONNECTION**

TAP	VOLTS
1	504
2	491
3	480
4	466
5	458
6	445
7	432



**COIL TAP ARRANGEMENT**



**NET WGT**  
661 LB  
299.8 Kg  
89626  
UY74C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
COPPER CONDUCTOR      PRIMARY: 10 KV BIL      SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
**CHECK ADDITIONAL NEC AND LOCAL CODE**

X3	H3	X2	H2	X1	H1
-	-	-	-	-	-

Note: X0 at the bottom

Outline: 303B111GEUY74C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X3 H3 X2 H2 X1 H1  
X3 H3 X2 H2 X1 H1  
X3 H3 X2 H2 X1 H1

