



# Transformer

by ABB




\*1M000000\*

**Catalog Number**      **Type QL**  
**9T10C1334G31**


75.0 KVA    60 HZ    3 PH    6.2 % IMP  
40 C AMB.    115 C RISE    220 C SYSTEM    IS-19C

PRIMARY (X)    208 VOLTS (LINE-LINE)  
SECONDARY (H)    480 VOLTS (LINE-LINE)

JUMPER CONNECTION	TAP VOLTS
1	218
2	213
3	208
4	204
5	196
6	191
7	187




### COIL TAP ARRANGMENT



<b>NET WGT</b>	<b>INSPECTION &amp; FINAL TEST</b>
748 LB	
339.3 Kg	<b>NOG</b>
89700	<b>N139!</b>
UX74C	<b>092021</b>



H3	X3	H2	X2	H1	X1
-	-	-	-	-	-
H3	X3	H2	X2	H1	X1
-	-	-	-	-	-



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

H3	X3	H2	X2	H1	X1
-	-	-	-	-	-
Note: standard					

Outline: 303B111GEUXP74C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency