



Transformer

by ABB



1M000000


Catalog Number **Type QL**
9T10C1335G03

112.5 KVA 60 HZ 3 PH 5.9 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


PRIMARY (X) 208 VOLTS (LINE-LINE)
SECONDARY (H) 480 VOLTS (LINE-LINE)

JUMPER CONNECTION

TAP	VOLTS
1-2	224
2-3	213
3-4	208
4-5	202
5-6	196



COIL TAP ARRANGEMENT



NET WGT
790 LB
358.3 Kg
89702
DY75C

INSPECTION & FINAL TEST
NOG
N137!
091021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

ASSEMBLED IN MEXICO

H3 - H2 - H1 - -
- X3 - X2 - X1
Note: standard

Outline: 303B11GEDYP75C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

H3 - H2 - H1 - -
- X3 - X2 - X1

H3 - H2 - H1 - -
- X3 - X2 - X1

2M000000

3M000000