



# Transformer

—  
by ABB



\*1M000000\*


**Catalog Number**      **Type QL**  
**9T10C1337**

225.0 KVA    60 HZ    3 PH    5.3 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C

**JUMPER CONNECTION**

| TAP | VOLTS |
|-----|-------|
| 1-2 | 225   |
| 2-3 | 217   |
| 3-4 | 208   |
| 4-5 | 201   |
| 5-6 | 194   |


PRIMARY (X)    208 VOLTS (LINE-LINE)  
SECONDARY (H)    480 VOLTS (LINE-LINE)



|                |                         |
|----------------|-------------------------|
| <b>NET WGT</b> | INSPECTION & FINAL TEST |
| 1847 LB        | TEST                    |
| 837.8 Kg       | NOG                     |
| 89705          | N137!                   |
| DX77C          | 091021                  |



### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009**  
 COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

Note:

Outline: 303B112GEDXP77C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*



\*3M000000\*