



# Transformer

by ABB



\*1M000000\*


**Catalog Number**      **Type QL**  
**9T10C1337G81**

225.0 KVA    60 HZ    3 PH    4 % IMP  
40 C AMB.    80 C RISE    220 C SYSTEM    IS-19C


PRIMARY (X)    208 VOLTS (LINE-LINE)  
SECONDARY (H)    480 VOLTS (LINE-LINE)

**JUMPER CONNECTION**

TAP	VOLTS
1-2	221
2-3	214
3-4	208
4-5	201
5-6	195



**COIL TAP ARRANGMENT**



<b>NET WGT</b>	<b>INSPECTION &amp; FINAL TEST</b>
2150 LB	NOG
975.2 Kg	N137!
89707	091021
DX78C	



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009**  
 COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

Note:

Outline: 303B112GEDXP78C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*



\*3M000000\*