



Transformer

—
by ABB



1M000000


Catalog Number **Type QL**
9T10C1181

15.0 KVA 60 HZ 3 PH 4 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


Note: Design is based on 15.00KVA & 115C Rise 4% Imp.

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 240 VOLTS (LINE-LINE)
120 VOLTS (1 PH MIDTAP X1-X4)

JUMPER CONNECTION	TAP VOLTS
1	504
2	492
3	480
4	468
5	456
6	445
7	433



COIL TAP ARRANGEMENT



NET WGT	INSPECTION & FINAL TEST
230 LB	
104.3 Kg	NOG
89652	N139!
UX71C	092021



X3	H3	X2	H2	X1	H1	X4
-	-	-	-	-	-	-
X3	H3	X2	H2	X1	H1	X4
-	-	-	-	-	-	-



2M000000



3M000000

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X3 H3 X2 H2 X1 H1 X4

Note: MID-TAP

Outline: 303B111GEUXP71C