



# Transformer

by ABB



\*1M000000\*

**Catalog Number**  
**9T10C1341G31**


**Type** **QL**

15.0 KVA 60 HZ 3 PH 3.7 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 15.00KVA & 115C Rise 3.7% Imp.

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 480 VOLTS (LINE-LINE)  
277 VOLTS (LINE-NEUTRAL)


JUMPER CONNECTION	TAP VOLTS
1	219
2	213
3	208
4	203
5	197
6	193
7	187



NET WGT	INSPECTION & FINAL TEST
230 LB	
104.3 Kg	NOG
89713	N139!
UX71C	092021



### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1 H0

Note: **standard**

Outline: 303B111GEUXP71C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

H3 X3 H2 X2 H1 X1 H0

\*2M000000\*

H3 X3 H2 X2 H1 X1 H0

\*3M000000\*