



Transformer

by ABB




1M000000

Catalog Number **Type QL**
9T10C1184G02


75.0 KVA 60 HZ 3 PH 5.6 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 240 VOLTS (LINE-LINE)
120 VOLTS (1 PH MIDTAP X1-X4)

JUMPER CONNECTION	TAP VOLTS
1	504
2	492
3	480
4	468
5	456
6	444
7	432



COIL TAP ARRANGEMENT



NET WGT
661 LB
299.8 Kg
89655
UY74C

INSPECTION & FINAL TEST
NOG
N139!
092021



H1	-	-	-	-	-	-	-
X1	-	-	-	-	-	-	-
H2	-	-	-	-	-	-	-
X2	-	-	-	-	-	-	-
H3	-	-	-	-	-	-	-
X3	-	-	-	-	-	-	-
H4	-	-	-	-	-	-	-
X4	-	-	-	-	-	-	-



2M000000



3M000000

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X4 X3 H3 X2 H2 X1 H1

Note: MID-TAP

Outline: 303B111GEUY74C