



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10C1194G32 **Type** QL


75.0 KVA 60 HZ 3 PH 3.8 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 240 VOLTS (LINE-LINE)

JUMPER CONNECTION TAP	VOLTS
1	505
2	490
3	480
4	470
5	455
6	445
7	430



### COIL TAP ARRANGEMENT



**NET WGT**  
748 LB  
339.3 Kg  
89681  
UX74C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



X3 H3 X2 H2 X1 H1  
- - - - -  
X3 H3 X2 H2 X1 H1  
- - - - -

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1  
- - - - -  
Note: standard

Outline: 303B111GEUXP74C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

