



# Transformer

by ABB





\*1M000000\*

**Catalog Number**      **Type QL**  
**9T10C1196**

150.0 KVA    60 HZ    3 PH    4.5 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C

PRIMARY (H)      480 VOLTS (LINE-LINE)  
SECONDARY (X)    240 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	504
2-3	492
3-4	480
4-5	468
5-6	456
6-7	444
7-8	432



<b>NET WGT</b>	<b>INSPECTION &amp; FINAL TEST</b>
1085 LB	
492.2 Kg	<b>NOG</b>
89685	<b>N139!</b>
DY76C	<b>092021</b>



X3 - X2 - X1 - - H3 - H2 - H1  
X3 - X2 - X1 - - H3 - H2 - H1

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 COPPER CONDUCTOR      PRIMARY: 10 KV BIL      SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

**X3 - X2 - X1 - -**  
**- H3 - H2 - H1**  
 Note: standard

Outline: 303B111GEDYP76C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

